

Plug union, straight

STV-GE G3/8-AG 14

Part no.: 10.08.02.00211

<https://www.schmalz.com/10.08.02.00211>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-GE G3/8-AG 14

Push-in Fitting, straight



Thread G1: G3/8"-M

Hose diameter: 14 mm


Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 21.5 mm

Length L: 30.5 mm

Design Data



Attribute	Value
D	21.50 mm
d	14 mm
G1	G3/8"-M
dn	10.30 mm
L	30.50 mm
L1	37.80 mm
L2	22.10 mm
LG1	7.30 mm
SW1	22 mm

Technical Data

Attribute	Value
Hose type	Hose D = 14 d = 11
Hose type	14-11
Material	Brass
Pressure range (operating pressure)	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	50 g
Product family	STV

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Plug union, straight

STV-GE G3/8-AG 14

Part no.:10.08.02.00211

<https://www.schmalz.com/10.08.02.00211>

Accessories



VSL 14-11 PU MI-TR

Part no.:10.07.09.00038

External diameter D: 14 mm

Internal diameter d: 11 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 100 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au