

Connection (geared)

SXT-CON-GB-M-D25

Part no.:10.07.13.00112

<https://www.schmalz.com/10.07.13.00112>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Tooling System SXT > Connections (Geared) SXT-CON-GB > SXT-CON-GB-M-D25

Gear bracket for tube, modular, for swivel arms and to connect with Round Tooling




Material: Aluminum

Connection 1: D25

Shape: Male

Design Data



Attribute	Value
D	35 mm
d	25 mm
d1	8.50 mm
H	56 mm
H2	20 mm
L	39.50 mm
L2	21 mm
L3	17 mm

Technical Data

Attribute	Value
Material	Aluminum
Shape	Male
Weight	100 g
Product family	SXT

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Connection (geared)

SXT-CON-GB-M-D25

Part no.:10.07.13.00112

<https://www.schmalz.com/10.07.13.00112>

Accessories



SXT-CON-GB-F-D25

Part no.:10.07.13.00114

Material: Aluminum

Connection 1: D25

Shape: Female



SXT-CON-GB-F-D40

Part no.:10.07.13.00115

Material: Aluminum

Connection 1: D40

Shape: Female



SXT-CON-GB-F-1IN

Part no.:10.07.13.00191

Material: Aluminum

Connection 1: 1 Inch

Shape: Female

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Connection (geared)

SXT-CON-GB-M-D25

Part no...:10.07.13.00112

<https://www.schmalz.com/10.07.13.00112>



SXT-EXT-GB2-50

Part no...:10.07.13.00034

External diameter D: 25 mm

Length L: 50.8 mm

Material: Aluminum

Shape: Gear Bracket both sides



SXT-ANG-GB2-F

Part no...:10.07.13.00121

Material: Aluminum

Shape: Female

Shape: Gear Bracket both sides



SET SCHRAUBE FED-SCHE M8x70

Part no...:10.07.13.00179

Thread G: M8

Length L: 70 mm

Connection (geared)

SXT-CON-GB-M-D25

Part no...:10.07.13.00112

<https://www.schmalz.com/10.07.13.00112>



SET SCHRAUBE FED-SCHE M8x80

Part no...:10.07.13.00181

Thread G: M8

Length L: 80 mm



SET SCHRAUBE FED-SCHE M8x50

Part no...:10.07.13.00175

Thread G: M8

Length L: 50 mm