

Schmalz X-Pump

SXMPi 25 NO Q PC M12-5

Part no...:10.02.02.05287

<https://www.schmalz.com/10.02.02.05287>




Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Compact Ejectors > Compact Ejectors SXMPi Class B > SXMPi 25 NO Q PC M12-5

Compact ejector with Condition Monitoring, power blow-off function and pneu. air-saving function



Nozzle diameter:	2.5 mm
Electrical connection:	Male connect M12, 5 pol
Suction rate (max.):	185 l/min
Air consumption suction:	290 l/min
Pressure range (operating pressure):	3.0 ... 6.0 bar
Max. vacuum:	-850 mbar
Control valve:	Normally open
Function:	Pressure Control
Protection type IP:	IP 65
Sound level free:	67 dB(A)
Communication:	IO-Link (Class B)

Design Data



Attribute	Value
B	39 mm
d	5.50 mm
G2	M12x1-M
H	108 mm
H1	146 mm
H2	54 mm
H3	6 mm
H4	26 mm
L	210 mm
L2	5 mm
L3	97 mm
X1	89 mm
Y1	10 mm

Technical Data

Attribute	Value
Nozzle diameter	2.50 mm
Degree of evacuation	85 %

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Schmalz X-Pump

SXMPi 25 NO Q PC M12-5

Part no...:10.02.02.05287

<https://www.schmalz.com/10.02.02.05287>

Suction rate (max.)	185 l/min
Suction rate (max.)	11.10 m³/h
Suction rate (max.)	6.53 cfm
Air consumption suction	290 l/min
Air consumption suction	10.24 cfm
Air consumption suction	17.40 m³/h
Sound level free	67 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure range (operating pressure)	43.5 ... 87.0
Max. air consumption blow off	320 l/min
Air consumption blow off	11.30 cfm
Air consumption blow off	19.20 m³/h
Recomm. internal hose diameter compressed air	8 mm
Recomm. internal hose diameter vacuum	9 mm
Control valve	Normally open
Weight	0.96 kg
Operating temperature	0 ... 50 °C
Product family	SXMPi

Accessories



ASK B-M12-5 5000 S-M12-5

Part no...:21.04.05.00266

Cable length: 5,000 mm

Material hose: PUR cable

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Schmalz X-Pump

SXMPi 25 NO Q PC M12-5

Part no.:10.02.02.05287

<https://www.schmalz.com/10.02.02.05287>



ASK B-M12-5 2000 S-M12-5

Part no.:21.04.05.00211

Pressure range (operating pressure): bar

Electrical connection: Fem connect M12, 5 pol

Cable length: 2,000 mm

Material hose: PUR cable



ASK B-M12-5 5000 K-5P

Part no.:21.04.05.00080

Electrical connection: Fem connect M12, 5 pol

Cable length: 5,000 mm

Material hose: PUR cable

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au