

Flange plate robot application

FLAN-PL YAS-2

Part no.:10.03.01.00404

<https://www.schmalz.com/10.03.01.00404>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Generators End-of-Arm > FLAN-PL YAS-2

Flange plate (round)




Length L: 16 mm

Type: YAS-2

Type: Motoman-HC10

Design Data



Attribute	Value
d	40 mm
d1	6.60 mm
D	89 mm
D mk1	63 mm
D4	63.50 mm
L	16 mm
L1	35.30 mm

Accessories

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com

Flange plate robot application

FLAN-PL YAS-2

Part no...:10.03.01.00404

<https://www.schmalz.com/10.03.01.00404>



ECBPi 12 24V-DC M12-8

Part no...:10.03.01.00314

Suction rate (max.): 12 l/min

Rated power: 13 W

Voltage DC: 24V - DC

Rated current: 0.6 A

Electrical connection: Male connect M12, 8 pol

Max. vacuum: 750 mbar

Operating temperature: 5 ... 45 °C



ECBPi 12 24V-DC TB-8

Part no...:10.03.01.00364

Suction rate (max.): 12 l/min

Rated power: 13 W

Voltage DC: 24V - DC

Rated current: 0.6 A

Electrical connection: Terminal block 8x

Max. vacuum: 750 mbar

Operating temperature: 5 ... 45 °C

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com