


CobotPump (Mini) for electrical vacuum generation for collaborative robots



Voltage DC: 24V - DC
Rated current: 0.3 A
Electrical connection: Spring contact
Operating temperature: 0 ... 40 °C
Suction rate (max.): 1.6 l/min
Rated power: 7.2 W

Design Data



Attribute	Value
D	63 mm
D2	35.50 mm
D mk1	46 mm
G1	M4-F
G2	G1/4"-F
L	56.40 mm
L1	61.40 mm
LG1	6 mm
LG2	11 mm

Technical Data

Attribute	Value
Suction rate (max.)	1.60 l/min
Voltage DC	24V - DC
Rated power	7.20 W
Rated current	0.30 A
Electrical connection	Spring contact
Operating temperature	0 ... 40 °C

CobotPump

ECBPMi 24V-DC FK

Part no...:10.03.01.00500

<https://www.schmalz.com/10.03.01.00500>



Spare parts



SPB1 30 ED-65 G1/8-AG

Part no...:10.01.06.03496

Size: 30

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/8"-M

Number of folds: 1.5

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au