

Flat suction cup (round)

PFG 40 NBR-55 N007

Part no.: 10.01.01.00016

<https://www.schmalz.com/10.01.01.00016>

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 40

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	6 mm
d1	11 mm
Dk	24.30 mm
Dmax(S)	43 mm
Ds	40 mm
H	14 mm
H2	7 mm
Z (Stroke)	3.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	57.70 N
Volume	3.91 cm ³
Curve radius (min) (convex)	50 mm
Size	40
Nipple family	N 007
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	7.60 g

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Flat suction cup (round)

PFG 40 NBR-55 N007

Part no.:10.01.01.00016

<https://www.schmalz.com/10.01.01.00016>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N007 G1/8-AG DN240

Part no.:10.01.01.03531

Nipple family: N 007

Thread G1: G1/8"-M

Length L1: 21 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2.4 mm

Material: Aluminum

Spanner size SW2: 4 mm



SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

Nipple family: N 007

Thread G1: G1/8"-F

Length L1: 24.5 mm

Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Spanner size SW2: 4 mm



SU 40

Part no.:10.01.01.12856

Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au



Flat suction cup (round)

PFG 40 NBR-55 N007

Part no...:10.01.01.00016

<https://www.schmalz.com/10.01.01.00016>

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au