

Holder system

HTS-A3 SGM-HP 30/40 OP

Part no...:10.01.17.00557

<https://www.schmalz.com/10.01.17.00557>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > Holder System Magnetic Grippers
SGM-HP/-HT > HTS-A3 SGM-HP 30/40 OP

Holder system




Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper SGM-HP

Size: 30/40

Design Data



Attribute	Value
B	26 mm
d	4.50 mm
D	28.50 mm
H	9.40 mm
H1	48.30 mm
H2	6 mm
H3	27.10 mm
H4	35 mm
L	84 mm
X1	74 mm
Y1	12 mm

Technical Data

Attribute	Value
Size	30/40
Material	Aluminum
Weight	86 g
Size	30/40

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Holder system

HTS-A3 SGM-HP 30/40 OP

Part no...:10.01.17.00557

<https://www.schmalz.com/10.01.17.00557>

Accessories



HTR-UNI 2N X3

Part no...:10.01.03.00302

Suction cup connection: ball head 28.5 mm

Operating temperature: °C

Cross-beam connection: 2 T-slots