

Bellows suction cups (round)

SAXB 50 ED-85 G3/8-IG

Part no.:10.01.42.00008

<https://www.schmalz.com/10.01.42.00008>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bellows suction cups SAXB > SAXB 50 ED-85 G3/8-IG

High-speed bellows suction cup for adaptation to strongly curved and oiled surfaces



Size: 50

Suction cup material: Elastodur ED


Material hardness [Shore A]: 85 Shore A

Nipple material: Aluminum

Connection: G3/8-IG

Number of folds: 1.5

Design Data



Attribute	Value
dn	6.10 mm
Dmax(S)	55 mm
Ds	49.60 mm
D1	43.20 mm
G1	G3/8"-F
H	36.90 mm
LG1	13 mm
SW1	22 mm
Z (Stroke)	11.60 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	58 N
Lateral force	78 N
Lateral force (oily surface)	67 N
Volume	18.90 cm ³
Curve radius (min) (convex)	22 mm
Hose diameter (rec.) d	6 mm
Size	50
Connection	G3/8"-F

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Bellows suction cups (round)

SAXB 50 ED-85 G3/8-IG

Part no...:10.01.42.00008

<https://www.schmalz.com/10.01.42.00008>

Number of folds	1.50
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	26.40 g
Product family	SAXB