

Bellows suction cups (round)

SAXB 80 ED-85 G1/4-IG

Part no.: 10.01.42.00010

<https://www.schmalz.com/10.01.42.00010>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bellows suction cups SAXB > SAXB 80 ED-85 G1/4-IG

High-speed bellows suction cup for adaptation to strongly curved and oiled surfaces



Size: 80

Suction cup material: Elastodur ED


Material hardness [Shore A]: 85 Shore A

Nipple material: Brass

Connection: G1/4-IG

Number of folds: 1.5

Design Data



Attribute	Value
Dmax(S)	91 mm
Ds	81 mm
D1	54.10 mm
G1	G1/4"-F
H	55 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	22.20 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	150 N
Lateral force	176 N
Lateral force (oily surface)	155 N
Volume	70.70 cm ³
Curve radius (min) (convex)	32.50 mm
Hose diameter (rec.) d	6 mm
Size	80
Connection	G1/4"-F

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Bellows suction cups (round)

SAXB 80 ED-85 G1/4-IG

Part no...:10.01.42.00010

<https://www.schmalz.com/10.01.42.00010>

Number of folds	1.50
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	53.20 g
Product family	SAXB