

Bellows suction cups (round)

SAXB 60 ED-85 G3/8-AG

Part no.:10.01.42.00022

<https://www.schmalz.com/10.01.42.00022>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bellows suction cups SAXB > SAXB 60 ED-85 G3/8-AG

High-speed bellows suction cup for adaptation to strongly curved and oiled surfaces



Size: 60

Suction cup material: Elastodur ED


Material hardness [Shore A]: 85 Shore A

Nipple material: Aluminum

Connection: G3/8-AG

Number of folds: 1.5

Design Data



Attribute	Value
Dmax(S)	66 mm
Ds	59.60 mm
D1	49.40 mm
G1	G3/8"-M
H	41.30 mm
LG1	10 mm
SW1	22 mm
Z (Stroke)	14.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	90 N
Lateral force	105 N
Lateral force (oily surface)	81 N
Volume	31.90 cm ³
Curve radius (min) (convex)	30 mm
Hose diameter (rec.) d	6 mm
Size	60
Connection	G3/8"-M

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Bellows suction cups (round)

SAXB 60 ED-85 G3/8-AG

Part no...:10.01.42.00022

<https://www.schmalz.com/10.01.42.00022>

Number of folds	1.50
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	41 g
Product family	SAXB