

Dust filter

STF 75 P 8.0 SSD

Part no.:10.07.01.00263

<https://www.schmalz.com/10.07.01.00263>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Blowers > STF 75 P 8.0 SSD

Dust filter



Connection: $\varnothing 75\text{mm}$


Shape: Piclon housing

Nominal flow rate: $480\text{ m}^3/\text{h}$

Filter pore size: $3\text{ }\mu\text{m}$

Additional function: Hose clamps SSD

Design Data



Attribute	Value
B1	300 mm
B2	168 mm
d	8.50 mm
D	228 mm
D1	240 mm
D2	75 mm
D3	75 mm
H	250.60 mm
L	439 mm
L1	579 mm
L2	140 mm
X1	240 mm

Technical Data

Attribute	Value
Connection	$\varnothing 75\text{mm}$
Nominal flow rate	$480\text{ m}^3/\text{h}$
Nominal flow rate	$8000\text{ l}/\text{min}$
Max. vacuum	-500 mbar
Filter pore size	$3\text{ }\mu\text{m}$
Weight	2.60 kg

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Dust filter

STF 75 P 8.0 SSD

Part no...:10.07.01.00263

<https://www.schmalz.com/10.07.01.00263>

Product family

VF

Spare parts



FILT-EINS 3 159x376 STF-Picl-8

Part no...:10.07.01.00079

Filter pore size: 3 µm

External diameter D: 159.2 mm

Length L: 376 mm

Construction use: Dust filter STF

Size: Picl-8

Type: 480m³/h