

Hose clamp

SSD 85-90 ST-VZ

Part no...:10.07.10.00102

<https://www.schmalz.com/10.07.10.00102>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSD 85-90 ST-VZ

Hose clamp for securing wire-reinforced hoses




Clamping range: 85.0 ... 90.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	85 mm
d2	90 mm
L	19 mm

Technical Data

Attribute	Value
Clamping range	85.0 ... 90.0 mm
Material	Steel
Weight	46.10 g
Product family	SSB / SSD

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Hose clamp

SSD 85-90 ST-VZ

Part no.:10.07.10.00102

<https://www.schmalz.com/10.07.10.00102>

Accessories



VSL 86-75 PU-DS-AS TR

Part no.:10.07.09.00054

External diameter D: 86 mm

Internal diameter d: 75 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 66 mm

Pressure range (operating pressure): -0.50 ... 1.69 bar

Operating temperature: -40 ... 90 °C



VSL 85-75 PVC-PS GR

Part no.:10.07.09.00048

External diameter D: 85 mm

Internal diameter d: 75 mm

Length max.: 10 m

Material hose: PVC with PVC-spiral

Bending radius min.: 114 mm

Pressure range (operating pressure): -0.29 ... 1.00 bar

Operating temperature: -20 ... 70 °C



VSL 87-75 PU-DS-AS

Part no.:10.07.09.00061

External diameter D: 87 mm

Internal diameter d: 75 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 195 mm

Pressure range (operating pressure): -1.00 ... 2.36 bar

Operating temperature: -40 ... 90 °C

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca