

Hose clamp

SSD 60-68 ST-VZ

Part no...:10.07.10.00017

<https://www.schmalz.com/10.07.10.00017>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSD 60-68 ST-VZ

Hose clamp for securing wire-reinforced hoses




Clamping range: 60.0 ... 68.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	60 mm
d2	68 mm
L	15 mm

Technical Data

Attribute	Value
Clamping range	60.0 ... 68.0 mm
Material	Steel
Weight	46 g
Product family	SSB / SSD

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca


Hose clamp

SSD 60-68 ST-VZ

Part no.: 10.07.10.00017

<https://www.schmalz.com/10.07.10.00017>

Accessories



VSL 60-50 PU-DS-AS KL-TR

Part no.: 10.07.09.00020

External diameter D: 60 mm

Internal diameter d: 50 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.82 ... 2.48 bar

Operating temperature: -40 ... 90 °C



VSL 61-50 PVC-DS GR

Part no.: 10.07.09.00033

External diameter D: 61 mm

Internal diameter d: 50 mm

Length max.: 10 m

Material hose: PVC with wire spiral

Bending radius min.: 90 mm

Pressure range (operating pressure): -0.78 ... 1.50 bar

Operating temperature: -20 ... 70 °C

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca