

## Compressed-air hose


VSL 8-6 PE BL

Part no.:10.07.09.00015

<https://www.schmalz.com/10.07.09.00015>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 8-6 PE BL

### Compressed-air hose



External diameter D: 8 mm

Internal diameter d: 6 mm


Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C

### Design Data



| Attribute | Value |
|-----------|-------|
| d         | 6 mm  |
| D         | 8 mm  |

### Technical Data

| Attribute                           | Value     |
|-------------------------------------|-----------|
| Hose type                           | 8-6       |
| Pressure range (operating pressure) | bar       |
| Operating temperature               | °C        |
| Length max.                         | 100 m     |
| Weight/Meter                        | 203 g/m   |
| Weight/Meter                        | 0.20 kg/m |
| Material hose                       | PE        |
| Product family                      | VSL       |

### Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Compressed-air hose

VSL 8-6 PE BL

Part no.:10.07.09.00015

<https://www.schmalz.com/10.07.09.00015>

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

### Accessories



#### ST G1/4-AG 6 MS-V

Part no.:10.08.03.00156

Thread G1: G1/4"-M

Hose diameter (rec.) d: 6 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4.5 mm



#### ST G1/8-AG 6 MS-V

Part no.:10.08.03.00154

Thread G1: G1/8"-M

Hose diameter (rec.) d: 6 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4.4 mm



#### STV-GE G1/4-AG 8

Part no.:10.08.02.00207

Thread G1: G1/4"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 13.9 mm

Length L: 17.8 mm

### Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Compressed-air hose

VSL 8-6 PE BL

Part no...:10.07.09.00015

<https://www.schmalz.com/10.07.09.00015>



### STV-GE G1/8-AG 8

Part no...:10.08.02.00206

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

External diameter D: 14 mm

Length L: 20.7 mm



### STV-GE G3/8-AG 8

Part no...:10.08.02.00237

Thread G1: G3/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 14.6 mm

Length L: 17.4 mm



### STVI-GE G1/4-IG 8

Part no...:10.08.02.00154

Thread G1: G1/4"-F

Hose diameter: 8 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 14.5 mm

Length L: 33.5 mm

## Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Compressed-air hose

VSL 8-6 PE BL

Part no.:10.07.09.00015

<https://www.schmalz.com/10.07.09.00015>



### STVI-GE G1/8-IG 8

Part no.:10.08.02.00151

Thread G1: G1/8"-F

Hose diameter: 8 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 14.5 mm

Length L: 29.5 mm



### STV-T G1/4-AG 8

Part no.:10.09.02.00043

Thread G1: G1/4"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

Length L: 48.5 mm



### STV-T G1/8-AG 8

Part no.:10.09.02.00041

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

Length L: 48.7 mm

## Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Compressed-air hose

VSL 8-6 PE BL

Part no...:10.07.09.00015

<https://www.schmalz.com/10.07.09.00015>



### STV-W G1/4-AG 8

Part no...:10.08.02.00161

Thread G1: G1/4"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 24 mm



### STV-W G1/8-AG 8

Part no...:10.08.02.00160

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 24 mm



### STV-W G3/8-AG 8

Part no...:10.08.02.00236

Thread G1: G3/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 23.7 mm

## Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Compressed-air hose

VSL 8-6 PE BL

Part no...:10.07.09.00015

<https://www.schmalz.com/10.07.09.00015>



### STV-WF G1/4-AG 8

Part no...:10.08.02.00171

Thread G1: G1/4"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 25.6 mm



### STV-WF G1/8-AG 8

Part no...:10.08.02.00170

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 23.4 mm



### STV-WF G3/8-AG 8

Part no...:10.08.02.00234

Thread G1: G3/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 26.7 mm

## Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Compressed-air hose

VSL 8-6 PE BL

Part no...:10.07.09.00015

<https://www.schmalz.com/10.07.09.00015>



### SVB-T 8

Part no...:10.09.02.00022

Hose diameter: 8 mm

Material: Brass

Operating temperature: -20 ... 80 °C

Length L: 49 mm