

## Hose sleeve

ST G1-1/4-AG 32 MS-V

Part no.:10.08.03.00169

<https://www.schmalz.com/10.08.03.00169>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1-1/4-AG 32 MS-V

### Hose sleeve



Thread G1: G1-1/4"-M

Hose diameter (rec.) d: 32 mm


Material: Brass

Surface: nickel plated

Length L: 10.3 mm

Nominal diameter dn: 27.9 mm

### Design Data



| Attribute | Value     |
|-----------|-----------|
| dn        | 27.90 mm  |
| D         | 32 mm     |
| G1        | G1-1/4"-M |
| L         | 10.30 mm  |
| L1        | 62 mm     |
| LG1       | 15.90 mm  |
| SW1       | 46 mm     |

### Technical Data

| Attribute | Value |
|-----------|-------|
| Material  | Brass |
| Weight    | 251 g |

### Accessories

#### Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Hose sleeve

ST G1-1/4-AG 32 MS-V

Part no...:10.08.03.00169

<https://www.schmalz.com/10.08.03.00169>



### VSL 41-32 PVC-DS KL-TR

Part no...:10.07.09.00008

External diameter D: 41 mm

Internal diameter d: 32 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 110 mm

Pressure range (operating pressure): -0.85 ... 4.00 bar

Operating temperature: -15 ... 65 °C

### Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)