

Bellows suction cup (round)

FGA 30 VU1-72 N013

Part no.:10.01.06.00177

<https://www.schmalz.com/10.01.06.00177>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FGA 30 VU1-72 N013

Bellows suction cup (round) with optimal adaptation to uneven surfaces




Size: 30

Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
d	8 mm
d1	15 mm
d2	17 mm
D1	30 mm
Dk	18 mm
Dmax(S)	31.50 mm
Ds	29 mm
H	27 mm
H2	12 mm
H3	16 mm
Z (Stroke)	8.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	1.50
Suction force (-600mbar)	13.50 N
Pull-off force	32 N
Volume	5.76 cm ³
Curve radius (min) (convex)	20 mm
Size	30

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Bellows suction cup (round)

FGA 30 VU1-72 N013

Part no.:10.01.06.00177

<https://www.schmalz.com/10.01.06.00177>

Suction cup material	Vulkollan VU1
Weight	6.50 g
Product family	FGA

Accessories



SA-NIP N013 G1/4-AG DN350

Part no.:10.01.06.00183

Thread G1: G1/4"-M

Fitting length: 5 mm

Material: Aluminum

External diameter D: 12.5 mm

Nominal size: 350

Spanner size SW2: 5 mm



SA-NIP N013 G1/4-IG DN350

Part no.:10.01.06.00180

Thread G1: G1/4"-F

Fitting length: 15 mm

Material: Aluminum

External diameter D: 12.5 mm

Spanner size SW2: 5 mm

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca