

Bellows suction cup HT2 (round)

SAB 60 HT2-65 G1/4-IG

Part no.: 10.01.06.03449

<https://www.schmalz.com/10.01.06.03449>

Home > Bellows Suction Cups SAB HT2 (1.5 Folds) > SAB 60 HT2-65 G1/4-IG

Bellows suction cup (round) for handling hot workpieces



Size: 60

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A


Temperature resistance: 200 °C

Nipple material: Aluminum

Connection: G1/4-IG

Number of folds: 1.5

Design Data



Attribute	Value
dn	6 mm
D1	49.50 mm
Dmax(S)	67 mm
Ds	61.20 mm
G1	G1/4"-F
H	46.30 mm
LG1	20 mm
SW1	22 mm
Z (Stroke)	14.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	82 N
Pull-off force	136 N
Lateral force	126 N
Volume	32 cm ³
Curve radius (min) (convex)	30 mm
Hose diameter (rec.) d	6 mm
Size	60
Connection	G1/4"-F
Suction cup material	High temperature material HT2

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Bellows suction cup HT2 (round)

SAB 60 HT2-65 G1/4-IG

Part no...:10.01.06.03449

<https://www.schmalz.com/10.01.06.03449>

Material hardness [Shore A]	65 Shore A
Weight	65.10 g
Number of folds	1.50
Product family	SAB
