

## Flat suction cup (round)

PFG 3.5 SI-CO-55 N003

Part no.:10.01.01.00752

<https://www.schmalz.com/10.01.01.00752>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 3.5 SI-CO-55 N003

### Flat suction cup (round) for smooth or slightly rough surfaces




Size: 3.5

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

### Design Data



Attribute	Value
d	2 mm
d1	3 mm
Dk	4.20 mm
Dmax(S)	4 mm
Ds	3.50 mm
H	4 mm
H2	1.50 mm
H3	2.50 mm
Z (Stroke)	0.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

Attribute	Value
Suction force (-600mbar)	0.42 N
Volume	0.02 cm <sup>3</sup>
Curve radius (min) (convex)	7.50 mm
Size	3.50
Nipple family	N 003
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55 Shore A
Product family	PFG

### Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Flat suction cup (round)

PFG 3.5 SI-CO-55 N003

Part no...:10.01.01.00752

<https://www.schmalz.com/10.01.01.00752>

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SA-NIP N003 M3-AG DN100

Part no...:10.01.01.00316

Thread G1: M3-M

Length L1: 7.5 mm

Fitting length: 2 mm

Material: Aluminum