

Flat suction cup (round)

SG 25 NBR-55 N027

Part no.:10.01.01.00196

<https://www.schmalz.com/10.01.01.00196>

Flat suction cup (round)




Size: 25

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 31 mm

Design Data



Attribute	Value
d	8 mm
Dk	12 mm
Dmax(S)	27 mm
Ds	25 mm
H	31 mm
H2	18 mm
Z (Stroke)	5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	0
Size	25
Suction cup material	Nitrile rubber NBR
Suction force (-600mbar)	24 N
Material hardness [Shore A]	55 Shore A
Product family	SG


Flat suction cup (round)

SG 25 NBR-55 N027

Part no.:10.01.01.00196

<https://www.schmalz.com/10.01.01.00196>

Accessories



SA-NIP N027 G1/8-AG DN350

Part no.:10.01.01.00320

Thread G1: G1/8"-M

Fitting length: 3 mm

Material: Aluminum