

Flat suction cup (round)

SGA 9 SI-55 N028

Part no.:10.01.01.00348

<https://www.schmalz.com/10.01.01.00348>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SGA 9 SI-55 N028

Flat suction cup (round)




Size: 9

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	5 mm
d1	7 mm
Dk	9 mm
Dmax(S)	9 mm
Ds	8 mm
H	12 mm
H2	2 mm
H3	4 mm
Z (Stroke)	1.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Size	9
Suction cup material	Silicone SI
Suction force (-600mbar)	2.10 N
Material hardness [Shore A]	55 Shore A
Volume	0.20 cm ³
Curve radius (min) (convex)	10 mm
Number of folds	0

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Flat suction cup (round)

SGA 9 SI-55 N028

Part no...:10.01.01.00348

<https://www.schmalz.com/10.01.01.00348>

Weight	0.40 g
Product family	SGA

Accessories



SA-NIP N028 M5-AG DN200

Part no...:10.01.01.00753

Thread G1: M5-M

Fitting length: 5 mm

Material: Aluminum



SA-NIP N028 M5-IG DN200

Part no...:10.01.01.00813

Thread G1: M5-F

Fitting length: 10 mm

Material: Aluminum

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca