

Bell suction cup (oval)

SAOG-S 80x30 NBR-60 M10-AG

Part no.:10.01.01.12303

<https://www.schmalz.com/10.01.01.12303>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAOG-S > SAOG-S 80x30 NBR-60 M10-AG

Bell suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 80x30

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Steel

Connection: M10-AG

Design Data



Attribute	Value
Bmax(S)	37.50 mm
Bs	30.90 mm
dn	4 mm
G1	M10-M
H	33.50 mm
LG1	10 mm
Lmax(S)	86.50 mm
Ls	80.90 mm
SW1	16 mm
Z (Stroke)	6 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	105 N
Lateral force	130 N
Lateral force (oily surface)	91 N
Volume	11 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Dimensions (LxB)	80 x 30
Suction cup material	Nitrile rubber NBR

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca



Bell suction cup (oval)

SAOG-S 80x30 NBR-60 M10-AG

Part no...:10.01.01.12303

<https://www.schmalz.com/10.01.01.12303>

Number of folds	0
Weight	34.10 g
Product family	SAOG-S

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca