

Solenoid valve

EMVP 32 24V-DC 3/2 NO

Part no.:10.05.02.00068

<https://www.schmalz.com/10.05.02.00068>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMVP > EMVP 32 24V-DC 3/2 NO

Solenoid valve EMVP for vacuum, pneumatic pilot control



Nominal size: 32 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Normally open


Connecting thread: G1-1/4"-F

Pressure range (operating pressure): bar

Nominal flow rate: 130 m³/h

Weight: 0.5 kg

Design Data



Attribute	Value
B	90.50 mm
B1	101 mm
B2	61.50 mm
D	80 mm
G1	G1-1/4"-F
G2	G1-1/4"-F
G3	G3/4"-F
G4	G1/8"-F
G5	G1/8"-F
H	101 mm
L	160 mm
L1	200.50 mm
X1	33 mm

Technical Data

Attribute	Value
Nominal size	32 mm
Nominal flow rate	130 m ³ /h
Control valve	Normally open
Nominal flow rate	2,166.70 l/min

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Solenoid valve


EMVP 32 24V-DC 3/2 NO

Part no...:10.05.02.00068

<https://www.schmalz.com/10.05.02.00068>

Power consumption DC	5 W
Voltage DC	24V - DC
Closing time	300 ms
Weight	0.50 kg
Product family	EMVP

Accessories



FAS 80x39 G3/4-AG

Part no...:10.05.01.00062

External diameter D: 80 mm

Length L: 39 mm

Thread G1: G3/4"-M



STEC 4 S-M12-4 St

Part no...:10.05.02.00157

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca