

Flat suction cup (round)

SUF 15 HT1-60 M5-AG

Part no.:10.01.01.14179

<https://www.schmalz.com/10.01.01.14179>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 15 HT1-60 M5-AG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



Size: 15

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Vacuum connection: M5-M

Design Data



Attribute	Value
Dmax(S)	16.80 mm
Ds	15 mm
dn	1.80 mm
G1	M5-M
H	13.90 mm
LG1	4.70 mm
SW1	8 mm
Z (Stroke)	1.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	9 N
Pull-off force	9 N
Volume	0.22 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	15
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Flat suction cup (round)

SUF 15 HT1-60 M5-AG

Part no.:10.01.01.14179

<https://www.schmalz.com/10.01.01.14179>

Weight	1.90 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC 030 M5-AG

Part no.:10.01.06.02802

Connection geometry: 030

Connection: M5-M

Length L1: 15.5 mm

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm



SUF 15 HT1-60 SC030

Part no.:10.01.01.13989

Size: 15

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A