

Bellows suction cups (round)

SFB1 15 HT1-60 G1/8-IG

Part no.:10.01.06.04402

<https://www.schmalz.com/10.01.06.04402>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFB1 15 HT1-60 G1/8-IG

Bellows suction cup (round) for very uneven workpieces flexible workpieces




Size: 15

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
G1	G1/8"-F
Dmax(S)	16 mm
Ds	15 mm
d2	4.70 mm
dn	4.10 mm
LG1	8 mm
H	30 mm
SW1	14 mm
Z (Stroke)	4 mm

Technical Data

Attribute	Value
Size	15
Suction cup material	High temperature material HT1
Suction force (-600mbar)	1 N
Product family	SFB1
Volume	0.80 cm ³
Number of folds	1.50
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Bellows suction cups (round)

SFB1 15 HT1-60 G1/8-IG

Part no.:10.01.06.04402

<https://www.schmalz.com/10.01.06.04402>

Spare parts



SFB1 15 HT1-60 SC040

Part no.:10.01.06.04380

Size: 15

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 1.5



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz GmbH | Eigentelstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch