

Bellows suction cups (round)

SFB1 20 SI-55 G1/8-AG

Part no.:10.01.06.04403

<https://www.schmalz.com/10.01.06.04403>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFB1 20 SI-55 G1/8-AG

Bellows suction cup (round) for very uneven workpieces flexible workpieces




Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Design Data



Attribute	Value
Dmax(S)	21 mm
Ds	20 mm
d2	6.60 mm
dn	4.10 mm
G1	G1/8-AG
LG1	7.50 mm
H	23.50 mm
SW1	14 mm
Z (Stroke)	5 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	2.10 N
Volume	1.20 cm ³
Size	20
Number of folds	1.50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Weight	5.60 g
Product family	SFB1

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Bellows suction cups (round)

SFB1 20 SI-55 G1/8-AG

Part no.:10.01.06.04403

<https://www.schmalz.com/10.01.06.04403>

Spare parts



SFB1 20 SI-55 SC040

Part no.:10.01.06.04369

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5



SC 040 G1/8-AG

Part no.:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20.2 mm

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz GmbH | Eigentelstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch