

Vacuum blower

SB 260 410 4 IE3-TYP1 ER

Part no...:10.04.01.00122

<https://www.schmalz.com/10.04.01.00122>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Blowers > Vacuum Blowers SB with Electro-Pneumatic Reversing > SB 260 410 4 IE3-TYP1 ER

Vacuum Blower for high suction rate



Suction rate (50 Hz): 260 m³/h

Suction rate (60 Hz): 305 m³/h

Vacuum (50 Hz): 410 mbar

Vacuum (60 Hz): 400 mbar

Rated power 50 Hz: 4 kW

Rated power 60 Hz: 4.8 kW

Construction: IE3:EU/CN/IND

Voltage at 50Hz: D230V/Y400V ±10%


Voltage at 60Hz: D265V/Y460V ±10%

Permission: UL/CSA

with: Electro-pneumatic reversing

Weight: 98 kg

Design Data



Attribute	Value
B	496 mm
B1	497 mm
d	13 mm
G1	G2"-M
H	573 mm
H2	134 mm
L	795 mm
X1	435 mm
Y1	446 mm

Technical Data

Attribute	Value
Suction rate (50 Hz)	260 m ³ /h
Max. vacuum	410 mbar
Rated power 50 Hz	4 kW
Protection type IP	IP 55
Weight	98 kg
Voltage at 50Hz	D230V/Y400V ±10%
Voltage at 60Hz	D265V/Y460V ±10%

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch



Vacuum blower

SB 260 410 4 IE3-TYP1 ER

Part no...:10.04.01.00122

<https://www.schmalz.com/10.04.01.00122>

Permission

UL/CSA

Product family

SB-ER

Contact Schmalz

Schmalz GmbH | Eigentalstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch