

Vacuum blower

SB 110 350 1.8 IE3-TYP2 ER

Part no.:10.04.01.00142

<https://www.schmalz.com/10.04.01.00142>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Blowers > Vacuum Blowers SB with Electro-Pneumatic Reversing > SB 110 350 1.8 IE3-TYP2 ER

Vacuum Blower for high suction rate



Suction rate (60 Hz): 110 m³/h

Vacuum (60 Hz): 350 mbar

Rated power 60 Hz: 1.8 kW

Construction: IE3:US/CAN


Voltage at 60Hz: YY230/Y460V ±10%

Permission: UL/CSA

with: Electro-pneumatic reversing

Weight: 64 kg

Design Data



Attribute	Value
B	306 mm
B1	480 mm
d	13 mm
G1	G2"-M
H	407 mm
H2	134 mm
L	776 mm
X1	435 mm
Y1	446 mm

Technical Data

Attribute	Value
Max. vacuum	350 mbar
Protection type IP	IP 55
Weight	64 kg
Voltage at 60Hz	YY230/Y460V ±10%
Permission	UL/CSA
Product family	SB-ER

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch



Vacuum blower

SB 110 350 1.8 IE3-TYP2 ER

Part no...:10.04.01.00142

<https://www.schmalz.com/10.04.01.00142>

Contact Schmalz

Schmalz GmbH | Eigentalstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch