

Vacuum blower

SB 470 290 4.8 IE3-TYP2 ER

Part no.:10.04.01.00151

<https://www.schmalz.com/10.04.01.00151>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Blowers > Vacuum Blowers SB with Electro-Pneumatic Reversing > SB 470 290 4.8 IE3-TYP2 ER

Vacuum Blower for high suction rate



Suction rate (60 Hz): 470 m³/h

Vacuum (60 Hz): 290 mbar

Rated power 60 Hz: 4.8 kW

Construction: IE3:US/CAN


Voltage at 60Hz: D230/Y460V

Permission: UL/CSA

with: Electro-pneumatic reversing

Weight: 74.5 kg

Design Data



Attribute	Value
B	452 mm
B1	505 mm
d	13 mm
G1	G2-1/2"-M
H	504 mm
H2	134 mm
L	863 mm
X1	435 mm
Y1	446 mm

Technical Data

Attribute	Value
Max. vacuum	290 mbar
Protection type IP	IP 55
Weight	74.50 kg
Voltage at 60Hz	D230/Y460V
Permission	UL/CSA
Product family	SB-ER

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch



Vacuum blower

SB 470 290 4.8 IE3-TYP2 ER

Part no...:10.04.01.00151

<https://www.schmalz.com/10.04.01.00151>

Contact Schmalz

Schmalz GmbH | Eigentalstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 |
schmalz@schmalz.ch