

Sealing profile (meter)

DI-PROF 20x15 2K-SWG NK-20/55

Part no.:10.07.04.00040

<https://www.schmalz.com/10.07.04.00040>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Sealing Profiles > Sealing Profiles DI-PROF > DI-PROF 20x15 2K-SWG NK-20/55

Sealing section for construction of specific gripper solutions



Width B: 20 mm


Height H: 15 mm

Material type: 2 Comp. sponge rubber

Sealing material: Natural Rubber NK

Material hardness [Shore A]: 20 Shore A

Design Data



Attribute	Value
B	20 mm
B1	22 mm
B2	2 mm
B3	16 mm
H	15 mm
H1	33 mm
H2	6 mm
H3	6 mm
H4	12 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Technical Data

Attribute	Value
Sealing material	Natural Rubber NK
Weight	411.50 g
Material hardness [Shore A]	20 Shore A
Product family	DI-PROF

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch