

Bellows suction cup (round)

FG 20 NK-45 N016

Part no.:10.01.06.00455

<https://www.schmalz.com/10.01.06.00455>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 20 NK-45 N016

Bellows suction cup (round) for very uneven workpieces




Size: 20

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Number of folds: 2.5

Design Data



Attribute	Value
d	4.50 mm
d2	10.50 mm
D1	20 mm
Dk	10 mm
Dmax(S)	21 mm
Ds	20 mm
H	22.10 mm
H2	3.80 mm
H3	9 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	5.20 N
Pull-off force	12.10 N
Volume	2.30 cm ³
Curve radius (min) (convex)	30 mm
Size	20
Nipple family	N 016
Number of folds	2.50

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Bellows suction cup (round)

FG 20 NK-45 N016

Part no...:10.01.06.00455

<https://www.schmalz.com/10.01.06.00455>

Suction cup material	Natural Rubber NK
Material hardness [Shore A]	45 Shore A
Weight	2.20 g
Product family	FG

Accessories



SA-NIP N016 G1/8-AG DN350

Part no...:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N016 G1/8-IG DN350

Part no...:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Bellows suction cup (round)

FG 20 NK-45 N016

Part no.:10.01.06.00455

<https://www.schmalz.com/10.01.06.00455>



SA-NIP N016 M5-AG DN250

Part no.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum

Contact Schmalz

Schmalz GmbH | Eigentalstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch