

Bellows suction cup (round)

FG 12 NBR-55 N016

Part no.:10.01.06.00557

<https://www.schmalz.com/10.01.06.00557>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 12 NBR-55 N016

Bellows suction cup (round) for very uneven workpieces




Size: 12

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 2.5

Design Data



Attribute	Value
d	4.50 mm
d2	5 mm
D1	12 mm
Dk	10 mm
Dmax(S)	13 mm
Ds	12 mm
H	21 mm
H2	3.80 mm
H3	9 mm
Z (Stroke)	7 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1.18 N
Pull-off force	3.50 N
Volume	0.75 cm ³
Curve radius (min) (convex)	12.50 mm
Size	12
Nipple family	N 016
Number of folds	2.50

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Bellows suction cup (round)

FG 12 NBR-55 N016

Part no...:10.01.06.00557

<https://www.schmalz.com/10.01.06.00557>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	1.10 g
Product family	FG

Accessories



SA-NIP N016 G1/8-AG DN350

Part no...:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N016 G1/8-IG DN350

Part no...:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Bellows suction cup (round)

FG 12 NBR-55 N016

Part no...:10.01.06.00557

<https://www.schmalz.com/10.01.06.00557>



SA-NIP N016 M5-AG DN250

Part no...:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum