

Suction cup (round)

SAUG-SCG 20 NBR-ESD-55 602 B

Part no.:10.01.30.01083

<https://www.schmalz.com/10.01.30.01083>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCG > SAUG-SCG 20 NBR-ESD-55 602 B

Suction cup (round)



Size: 20


Height H: 22.5 mm

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Suct. cups: Bell. suct. cup f. SCG(S)

Design Data



Attribute	Value
Dmax (N)	39.60 mm
Dmax(S)	25 mm
dn	15 mm
Ds	21.50 mm
G1	M37x1-F
H	22.50 mm
LG1	5 mm
Z (Stroke)	3 mm

Technical Data

Attribute	Value
Size	20
Pressure range (operating pressure)	bar
Operating temperature	°C
Number of folds	1.50
Weight	15.40 g
Holding force	N
Air consumption	m³/h
Air consumption	l/min

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Suction cup (round)

SAUG-SCG 20 NBR-ESD-55 602 B

Part no...:10.01.30.01083

<https://www.schmalz.com/10.01.30.01083>

Material hardness [Shore A]	55 Shore A
Suction rate	m ³ /h
Suction rate	l/min
Suction cup material	Nitrile rubber NBR-ESD
Product family	SAUG-SCG

Spare parts



BCG 20 NBR-ESD-55 SC085

Part no...:10.01.06.04573

Size: 20

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz GmbH | Eigentalstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch