

Basic Ejector

SBP 15 G02 SDA

Part no.:10.02.01.00602

<https://www.schmalz.com/10.02.01.00602>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > Basic Ejectors SBP > SBP 15 G02 SDA

Basic ejector for universal use



Nozzle diameter: 1.5 mm

Add. function: Axial silencer

Degree of evacuation: 85 %


Connection: G1/8"(1)-G1/8"(2)

Pressure optimal: 4.5 bar

Suction rate (max.): 71 l/min

Air consumption suction: 105 l/min

Design Data



Attribute	Value
B	15 mm
d	4.20 mm
D	14 mm
G1	G1/8"-F
G2	G1/8"-F
H	34 mm
H1	42 mm
H2	5.20 mm
H3	14 mm
L	51.50 mm
L1	102 mm
L2	22 mm
L3	10 mm
L4	12.50 mm
LG1	8 mm
LG2	8 mm
SW1	14 mm
SW2	14 mm
X1	20 mm

Technical Data

Contact Schmalz

Schmalz GmbH | Eigentelstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Basic Ejector

SBP 15 G02 SDA

Part no.:10.02.01.00602

<https://www.schmalz.com/10.02.01.00602>

Attribute	Value
Nozzle diameter	1.50 mm
Degree of evacuation	85 %
Suction rate (max.)	4.30 m³/h
Suction rate (max.)	71 l/min
Air consumption suction	6.30 m³/h
Air consumption suction	105 l/min
Sound level free	72 dB(A)
Sound level suction	65 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure optimal	4.50 bar
Recomm. internal hose diameter compressed air	4 mm
Recomm. internal hose diameter vacuum	6 mm
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	43.5 ... 87.0
Suction rate (max.)	2.51 cfm
Air consumption suction	3.71 cfm
Weight	22 g
Product family	SBP

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Accessories



BEF-PL 110x44.5x3 SBP

Part no.:10.02.01.00511

Length L: 110 mm

Width B: 44.5 mm

Height H: 3 mm

Construction use: Basic ejector SBP

Basic Ejector

SBP 15 G02 SDA

Part no...:10.02.01.00602

<https://www.schmalz.com/10.02.01.00602>



SET SBP M4-IG

Part no...:10.02.01.00769

Length L: 50 mm

Width B: 14 mm

Construction use: Basic ejector SBP

Type: M4-IG



VFT G1/4-IG 80

Part no...:10.07.01.00119

Connection: G1/4"-F

Shape: Short filter insert

Nominal flow rate: 110 l/min

Nominal flow rate: 6.6 m³/h

Filter pore size: 80 µm



VS-V-W-D PNP K 3C-D

Part no...:10.06.02.00678

Measuring range: -1,0 ... 0,0 bar

Shape: Cube, digital display

Construction shape vacuum switch: PNP switching

Electrical connection: Cable

Inputs/outputs: 2 digital

Display: Display 3-color / 2-line

Protection type IP: IP 40

Contact Schmalz

Schmalz GmbH | Eigentelstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Basic Ejector

SBP 15 G02 SDA

Part no...:10.02.01.00602

<https://www.schmalz.com/10.02.01.00602>



VS-P10-W-D PNP K 3C-D

Part no...:10.06.02.00680

Measuring range: 0,0 ... 10,0 bar

Shape: Cube, digital display

Construction shape vacuum switch: PNP switching

Electrical connection: Cable

Inputs/outputs: 2 digital

Display: Display 3-color / 2-line

Protection type IP: IP 40

Spare parts



SD G1/8-AG 14x40

Part no...:10.02.01.00540

Thread G1: G1/8"-M

External diameter D: 14 mm

Length L: 40 mm

Contact Schmalz

Schmalz GmbH | Eigentalstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch