

## Bellows suction cup (round)

FG 32 NBR-55 N018

Part no.:10.01.06.00140

<https://www.schmalz.com/10.01.06.00140>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 32 NBR-55 N018

### Bellows suction cup (round) for very uneven workpieces




Size: 32

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 2.5

### Design Data



| Attribute  | Value    |
|------------|----------|
| d          | 8 mm     |
| d1         | 15 mm    |
| d2         | 16 mm    |
| D1         | 32.40 mm |
| Dk         | 18 mm    |
| Dmax(S)    | 33.50 mm |
| Ds         | 32 mm    |
| H          | 37.50 mm |
| H2         | 13 mm    |
| H3         | 17 mm    |
| Z (Stroke) | 15 mm    |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                   | Value                |
|-----------------------------|----------------------|
| Suction force (-600mbar)    | 12.06 N              |
| Pull-off force              | 36.90 N              |
| Volume                      | 9.77 cm <sup>3</sup> |
| Curve radius (min) (convex) | 35 mm                |
| Size                        | 32                   |
| Nipple family               | N 018                |

### Contact Schmalz

Schmalz GmbH | Eigentelstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | [schmalz@schmalz.ch](mailto:schmalz@schmalz.ch)

## Bellows suction cup (round)

FG 32 NBR-55 N018

Part no.:10.01.06.00140

<https://www.schmalz.com/10.01.06.00140>

|                             |                    |
|-----------------------------|--------------------|
| Number of folds             | 2.50               |
| Suction cup material        | Nitrile rubber NBR |
| Material hardness [Shore A] | 55 Shore A         |
| Weight                      | 9.50 g             |
| Product family              | FG                 |

### Accessories



#### SA-NIP N018 G1/4-AG DN440

Part no.:10.01.06.01065

Nipple family: N 018

Thread G1: G1/4"-M

Length L1: 28.8 mm

Fitting length: 4 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum



#### SA-NIP N018 G1/4-IG DN440

Part no.:10.01.06.01066

Nipple family: N 018

Thread G1: G1/4"-F

Length L1: 28.8 mm

Fitting length: 15 mm

Nominal diameter dn: 4.4 mm

Spanner size SW2: 5 mm

Material: Aluminum

### Contact Schmalz

Schmalz GmbH | Eigentalstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | [schmalz@schmalz.ch](mailto:schmalz@schmalz.ch)