

Hose clamp

SSD 57-62 ST-VZ

Part no.:10.07.10.00036

<https://www.schmalz.com/10.07.10.00036>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSD 57-62 ST-VZ

Hose clamp for securing wire-reinforced hoses




Clamping range: 57.0 ... 62.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	57 mm
d2	62 mm
L	15 mm

Technical Data

Attribute	Value
Clamping range	57.0 ... 62.0 mm
Material	Steel
Weight	29 g
Product family	SSB / SSD

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Hose clamp

SSD 57-62 ST-VZ

Part no.:10.07.10.00036

<https://www.schmalz.com/10.07.10.00036>

Accessories



VSL 60-50 PU-DS-AS KL-TR

Part no.:10.07.09.00020

External diameter D: 60 mm

Internal diameter d: 50 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.82 ... 2.48 bar

Operating temperature: -40 ... 90 °C