

Plug union, elbow

STV-WF G1/4-AG 10

Part no.: 10.08.02.00258

<https://www.schmalz.com/10.08.02.00258>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-WF G1/4-AG 10

Push-in Fitting, swivelling and lockable



Thread G1: G1/4"-M


Hose diameter: 10 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 27.8 mm

Design Data



Attribute	Value
d	10 mm
G1	G1/4"-M
dn	7.20 mm
D1	16.60 mm
H	10 mm
H1	23.90 mm
L	27.80 mm
L1	37.70 mm
LG1	6.70 mm
SW1	17 mm
SW3	20 mm

Technical Data

Attribute	Value
Hose type	Hose D = 10 d = 7
Hose type	10-7
Material	Nickel plated
Pressure range (operating pressure)	-0.95 ... 15.00 bar
Operating temperature	-10 ... 70 °C
Weight	64 g

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Plug union, elbow

STV-WF G1/4-AG 10

Part no.:10.08.02.00258

<https://www.schmalz.com/10.08.02.00258>

Product family

STV

Accessories



VSL 10-7 PE MI-TR

Part no.:10.07.09.00083

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PE

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -30 ... 70 °C



VSL 10-7 PU MI-TR

Réf. article.:10.07.09.00084

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 85 °C

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz