

Flat suction cup (oval)

SGO 7x3.5 NBR-55 N003

Part no.:10.01.01.00488

<https://www.schmalz.com/10.01.01.00488>

Flat suction cup (oval) for narrow or curved workpieces




Dimensions (LxB): 7 x 3.5

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
Bmax(S)	4.50 mm
Bs	3.50 mm
d	1.50 mm
dn	1.50 mm
Dk	6 mm
Lmax(S)	8 mm
Ls	7 mm
H	6 mm
H2	1.50 mm
Z (Stroke)	0.80 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1 N
Dimensions (LxB)	7 x 3.5
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	0.10 g
Product family	SGO

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (oval)

SGO 7x3.5 NBR-55 N003

Part no...:10.01.01.00488

<https://www.schmalz.com/10.01.01.00488>

Accessories



SA-NIP N003 M3-AG DN100

Part no...:10.01.01.00316

Thread G1: M3-M

Length L1: 7.5 mm

Fitting length: 2 mm

Material: Aluminum