

Flat suction cup (round)

SGA 7 SI-55 N028

Part no.:10.01.01.00347

<https://www.schmalz.com/10.01.01.00347>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SGA 7 SI-55 N028

Flat suction cup (round)




Size: 7

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	5 mm
d1	7 mm
Dk	9 mm
Dmax(S)	7.50 mm
Ds	7 mm
H	12 mm
H2	2 mm
H3	4 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Size	7
Suction cup material	Silicone SI
Suction force (-600mbar)	1.60 N
Material hardness [Shore A]	55 Shore A
Volume	0.19 cm ³
Curve radius (min) (convex)	7.50 mm
Number of folds	0

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

SGA 7 SI-55 N028

Part no...:10.01.01.00347

<https://www.schmalz.com/10.01.01.00347>

Weight	0.40 g
Product family	SGA

Accessories



SA-NIP N028 M5-AG DN200

Part no...:10.01.01.00753

Thread G1: M5-M

Fitting length: 5 mm

Material: Aluminum



SA-NIP N028 M5-IG DN200

Part no...:10.01.01.00813

Thread G1: M5-F

Fitting length: 10 mm

Material: Aluminum

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz