

Bellows suction cup HT1 (round)

SAB 30 HT1-60 G1/4-IG

Part no.:10.01.06.02723

<https://www.schmalz.com/10.01.06.02723>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > Bellows Suction Cups SAB HT1 (1.5 Folds) > SAB 30 HT1-60 G1/4-IG

Bellows suction cup (round) for markless handling of workpieces



Size: 30

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/4-IG

Number of folds: 1.5

Design Data



Attribute	Value
dn	4 mm
D1	32 mm
Dmax(S)	34 mm
Ds	30.60 mm
G1	G1/4"-F
H	28 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	9 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	22 N
Pull-off force	33 N
Lateral force	30 N
Lateral force (oily surface)	13 N
Volume	5.90 cm ³
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	4 mm
Size	30

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cup HT1 (round)

SAB 30 HT1-60 G1/4-IG

Part no...:10.01.06.02723

<https://www.schmalz.com/10.01.06.02723>

Number of folds	1.50
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	14.30 g
Product family	SAB