

Bell suction cup (round)

SAX 80 ED-85 RA

Part no.:10.01.19.00176

<https://www.schmalz.com/10.01.19.00176>

Home > Bell-Shaped Suction Cups SAX > SAX 80 ED-85 RA

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 80


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Connection: Rectangular adapter

Number of folds: 0

Design Data



Attribute	Value
dn	6.75 mm
Dmax(S)	92.20 mm
Ds	81 mm
H	39.20 mm
L4	31.80 mm
SW1	22 mm
Z (Stroke)	13.90 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	270 N
Lateral force	192 N
Lateral force (oily surface)	269 N
Volume	51 cm ³
Curve radius (min) (convex)	32.50 mm
Size	80
Connection	Rectangular adapter
Number of folds	0
Suction cup material	Elastodur ED

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bell suction cup (round)

SAX 80 ED-85 RA

Part no...:10.01.19.00176

<https://www.schmalz.com/10.01.19.00176>

Material hardness [Shore A]	85 Shore A
-----------------------------	------------

Weight	48.30 g
--------	---------

Product family	SAX
----------------	-----
