

Solenoid valve

EMVO 12 24V-DC 3/2 NC

Part no.:10.05.01.00049

<https://www.schmalz.com/10.05.01.00049>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMVO > EMVO 12 24V-DC 3/2 NC

Solenoid valve EMVO for direct control of vacuum



Nominal size: 12 mm

Voltage DC: 24V - DC


Function: 3/2-way valve

Control valve: Normally closed

Connecting thread: G1/2"-F

Power consumption DC: 31.9 W

Design Data



Attribute	Value
d	6.50 mm
D	80 mm
G1	G1/2"-F
G2	G1/2"-F
G3	G1/2"-F
H	60 mm
H1	135.50 mm
L	122 mm
L2	32 mm
X1	24 mm
Y1	40 mm

Technical Data

Attribute	Value
Nominal size	12 mm
Control valve	Normally closed
Nominal flow rate	350 l/min
Nominal flow rate	21 m³/h
Power consumption DC	31.90 W
Voltage DC	24V - DC

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Solenoid valve

EMVO 12 24V-DC 3/2 NC

Part no.:10.05.01.00049

<https://www.schmalz.com/10.05.01.00049>

Weight	1.20 kg
Product family	EMVO

Accessories



FAS 80x33.8 G1/2-AG

Part no.:10.05.01.00061

External diameter D: 80 mm

Length L: 33.8 mm

Thread G1: G1/2"-M