

Bell suction cup (round)

SAG 60 NBR-60 G3/8-IG

Part no.:10.01.01.12166

<https://www.schmalz.com/10.01.01.12166>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAG > SAG 60 NBR-60 G3/8-IG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 60


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G3/8-IG

Design Data



Attribute	Value
dn	6 mm
Dmax(S)	70.50 mm
Ds	63.50 mm
G1	G3/8"-F
H	31 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	10.60 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	122 N
Lateral force	153 N
Lateral force (oily surface)	80 N
Volume	22 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	6 mm
Size	60
Suction cup material	Nitrile rubber NBR

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de

Bell suction cup (round)

SAG 60 NBR-60 G3/8-IG

Part no...:10.01.01.12166

<https://www.schmalz.com/10.01.01.12166>

Material hardness [Shore A]	60 Shore A
Number of folds	0
Weight	31.10 g
Product family	SAG