

Flat suction cup (round)

SUF 40 SI-55 G1/8-IG

Part no.:10.01.01.14103

<https://www.schmalz.com/10.01.01.14103>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 40 SI-55 G1/8-IG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



Size: 40


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Vacuum connection: G1/8"-F

Design Data



Attribute	Value
Dmax(S)	44 mm
Ds	40 mm
dn	6.10 mm
G1	G1/8"-F
H	30 mm
LG1	8 mm
SW1	17 mm
Z (Stroke)	4 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	61 N
Pull-off force	61 N
Volume	3.80 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Size	40
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de

Flat suction cup (round)

SUF 40 SI-55 G1/8-IG

Part no.:10.01.01.14103

<https://www.schmalz.com/10.01.01.14103>

Weight	18.90 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC 050 G1/8-IG

Part no.:10.01.06.04308

Connection geometry: 050

Vacuum connection: G1/8"-F

Fitting length: 14 mm

Nominal diameter dn: 6.1 mm



SUF 40 SI-55 SC050

Part no.:10.01.01.13973

Size: 40

Suction cup material: Silicone SI

Material characteristics: FDA-compatible

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de