

Vacuum hose (meter)

VSL 19-13 PVC-DS KL-TR

Part no.:10.07.09.00016

<https://www.schmalz.com/10.07.09.00016>

Home > Vacuum Lifters and Crane Systems > Vacuum Lifting Device VacuMaster > Spare and Wear Parts Vacuum Lifting Devices VacuMaster > Spare Parts VacuMaster Basic / Comfort > VSL 19-13 PVC-DS KL-TR

Hose for vacuum and compressed-air systems



External diameter D: 19 mm

Internal diameter d: 13 mm

Length max.: 50 m


Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C

Design Data



Attribute	Value
d	13 mm
D	19 mm

Technical Data

Attribute	Value
Hose type	19-13
Pressure range (operating pressure)	-0.90 ... 5.00 bar
Operating temperature	-15 ... 65 °C
Bending radius min.	85 mm
Length max.	50 m
Weight/Meter	190 g/m
Weight/Meter	0.19 kg/m
Material hose	PVC with wire spiral

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de

Vacuum hose (meter)

VSL 19-13 PVC-DS KL-TR

Part no.:10.07.09.00016

<https://www.schmalz.com/10.07.09.00016>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSB 12-20 ST-VZ

Part no.:10.07.10.00159

Clamping range: 12.0 ... 20.0 mm

Material: Steel

Surface: galvanised



SSB 16-27 ST-VZ

Part no.:10.07.10.00002

Clamping range: 16.0 ... 27.0 mm

Material: Steel

Surface: galvanised



ST G1/2-AG 13 MS-V

Part no.:10.08.03.00162

Thread G1: G1/2"-M

Hose diameter (rec.) d: 13 mm

Material: Brass

Surface: nickel plated

Length L: 6 mm

Nominal diameter dn: 11 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de

Vacuum hose (meter)

VSL 19-13 PVC-DS KL-TR

Part no...:10.07.09.00016

<https://www.schmalz.com/10.07.09.00016>



ST G1/4-AG 13 MS-V

Part no...:10.08.03.00158

Thread G1: G1/4"-M

Hose diameter (rec.) d: 13 mm

Material: Brass

Surface: nickel plated

Length L: 5.5 mm

Nominal diameter dn: 7.5 mm



ST G3/4-AG 13 MS-V

Part no...:10.08.03.00164

Thread G1: G3/4"-M

Hose diameter (rec.) d: 13 mm

Material: Brass

Surface: nickel plated

Length L: 8 mm

Nominal diameter dn: 10.4 mm



ST G3/8-AG 13 MS-V

Part no...:10.08.03.00160

Thread G1: G3/8"-M

Hose diameter (rec.) d: 13 mm

Material: Brass

Surface: nickel plated

Length L: 5.9 mm

Nominal diameter dn: 10 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de