

Suction cup (round)

SAUG-SCGS 50 SI-HD-65

Part no...:10.01.30.00919

<https://www.schmalz.com/10.01.30.00919>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCGS > SAUG-SCGS 50 SI-HD-65

Suction cup (round)




Size: 50

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Design Data



Attribute	Value
D1	51 mm
Dmax (N)	25 mm
Dmax(S)	51.50 mm
dn	18.90 mm
Ds	50.30 mm
G1	M20x1-F
H	31.50 mm
LG1	5 mm
Z (Stroke)	4.20 mm

Technical Data

Attribute	Value
Size	50
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	24.30 g
Product family	SAUG-SCGS

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de

Suction cup (round)

SAUG-SCGS 50 SI-HD-65

Part no.:10.01.30.00919

<https://www.schmalz.com/10.01.30.00919>

Spare parts



FLSA 50 SI-HD-65

Part no.:10.01.06.03467

Size: 50

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de