

Mounting plate

BEF-PL 38x15x11.5 G1/4-IG SNG

Part no.:10.01.29.00403

<https://www.schmalz.com/10.01.29.00403>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Needle Grippers > Accessories Needle Grippers SNG-V > BEF-PL 38x15x11.5 G1/4-IG SNG

Mounting plate



Pressure range (operating pressure): bar

Length L: 38 mm


Width B: 15 mm

Height H: 11.5 mm

Thread G1: G1/4"-F

Construction use: Needle gripper

Design Data



Attribute	Value
B	15 mm
d	5.50 mm
G1	G1/4"-F
H	11.50 mm
H2	5 mm
L	38 mm
L2	20 mm
LG1	11.50 mm
X1	29 mm

Technical Data

Attribute	Value
Weight	14.20 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de