

Bell suction cup (oval)

SAOXM 80x30 ED-85 SC045-AR

Part no.:10.01.24.00002

<https://www.schmalz.com/10.01.24.00002>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > SAOXM 80x30 ED-85 SC045-AR

High-Speed bell shaped suction cup




Dimensions (LxB): 80 x 30

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Design Data



Attribute	Value
Bk	24.10 mm
Bmax(S)	41.50 mm
Bs	31.90 mm
d	12.80 mm
H	22.40 mm
H2	3 mm
Lk	74.30 mm
Ls	82.10 mm
Z (Stroke)	6 mm

Technical Data

Attribute	Value
Lateral force	110 N
Lateral force (oily surface)	134 N
Volume	13 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Nipple family	SC 045-AR
Dimensions (LxB)	80 x 30
Suction cup material	Elastodur ED

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de

Bell suction cup (oval)

SAOXM 80x30 ED-85 SC045-AR

Part no...:10.01.24.00002

<https://www.schmalz.com/10.01.24.00002>

Material hardness [Shore A]	85 Shore A
Weight	12.20 g
Number of folds	0
Product family	SAOXM