

Bell suction cup (round)

SAX 60 ED-85 M10-AG

Part no.: 10.01.19.00223

<https://www.schmalz.com/10.01.19.00223>

Home > Bell-Shaped Suction Cups SAX > SAX 60 ED-85 M10-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 60


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Connection: M10-M

Number of folds: 0

Design Data



Attribute	Value
dn	4.10 mm
Dmax(S)	69.70 mm
Ds	61.50 mm
G1	M10-M
H	33.40 mm
LG1	14.50 mm
SW1	22 mm
Z (Stroke)	10.90 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	154 N
Lateral force	107 N
Lateral force (oily surface)	155 N
Volume	25.20 cm ³
Curve radius (min) (convex)	30 mm
Size	60
Connection	M10-M
Number of folds	0
Suction cup material	Elastodur ED

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de

Bell suction cup (round)

SAX 60 ED-85 M10-AG

Part no...:10.01.19.00223

<https://www.schmalz.com/10.01.19.00223>

Material hardness [Shore A]	85 Shore A
-----------------------------	------------

Weight	38.50 g
--------	---------

Product family	SAX
----------------	-----
