

Flat suction cup (round)

SAF 50 HT2-65 G1/4-IG

Part no.:10.01.01.12356

<https://www.schmalz.com/10.01.01.12356>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > Flat Suction Cups SAF HT2 > SAF 50 HT2-65 G1/4-IG

Flat suction cup (round) for very dynamic handling



Size: 50

Suction cup material: High temperature material HT2


Material hardness [Shore A]: 65 Shore A

Temperature resistance: 200 °C

Nipple material: Nickel plated

Connection: G1/4-IG

Design Data



Attribute	Value
dn	6 mm
Ds	50 mm
Dmax(S)	56 mm
G1	G1/4"-F
H	33 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	5 mm

Technical Data

Attribute	Value
Number of folds	0
Size	50
Suction force (-600mbar)	100 N
Temperature resistance	200 °C
Product family	SAF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de

Flat suction cup (round)

SAF 50 HT2-65 G1/4-IG

Part no.:10.01.01.12356

<https://www.schmalz.com/10.01.01.12356>

Accessories



SU 50

Part no.:10.01.01.12837

Size: 50

Clamping range: 45.0 ... 60.0 mm

Temperature resistance: 80 °C