

Edge gripper suction cup (oval)

SAOK 70x25 NBR-60 G3/8-IG

Part no.:10.01.01.12460

<https://www.schmalz.com/10.01.01.12460>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Edge Gripper Suction Cups SAOK (Oval) > SAOK 70x25 NBR-60 G3/8-IG

Edge gripper suction cup (oval) for dynamic handling of structured surfaces



Dimensions (LxB): 70 x 25


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Brass

Connection: G3/8-IG

Design Data



Attribute	Value
Bs	22.60 mm
dn	6 mm
G1	G3/8"-F
H	35.50 mm
LG1	9 mm
Lmax(S)	71 mm
Ls	67.20 mm
SW1	22 mm
Z (Stroke)	12.80 mm

Technical Data

Attribute	Value
Pull-off force	81 N
Pull-off force oily surface	60 N
Lateral force	46 N
Lateral force (oily surface)	20 N
Hose diameter (rec.) d	6 mm
Dimensions (LxB)	70 x 25
Workpiece angle (min)	80 °
Suction cup material	Nitrile rubber NBR

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es



Edge gripper suction cup (oval)

SAOK 70x25 NBR-60 G3/8-IG

Part no...:10.01.01.12460

<https://www.schmalz.com/10.01.01.12460>

Weight	47.80 g
Number of folds	0
Product family	SAOK

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Page 2 from 2